

Rittal – The System.

Faster – better – everywhere.



SV 3055.000 Busbar support

State: 23/05/2026 (Source: rittal.com/ie-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 3055.000 - Busbar support

For busbar systems 1250 A (100 mm), 1600 A (185 mm), 2500 A (150 mm), 3000 A (150 mm).



Features

Model No.	SV 3055.000
Material	Fibreglass-reinforced, thermoplastic polyester (PBT) Fire protection corresponding to UL 94-V0
Colour	RAL 7035
Number of poles	3-pole 150 mm
To fit busbars	60 x 10 80 x 10
Rated current max.	2,500 A
Dimensions	Width: 30 mm Height: 420 mm Depth: 160 mm
Packs of	2 pc(s).
Net weight	4.16 kg
Gross weight	4.503 kg
Customs tariff number	85469010
ETIM 9	EC001166
ETIM 8	EC001166
ECLASS 8.0	27400607

Features

Product description

SV Busbar support, 3-pole, 150 mm bar centre distance, for busbar
WH: 80x10 mm

Approvals

Explanations

Declaration of conformity
Declaration of conformity UK

Tender text

SV busbar support
for accommodating busbars. Suitable for busbars
up to 3 x 2 x 80 x 10 mm with inserts.

Rated operating voltage: 1000 V~, 50/60 Hz
to VDE 0660

Rated current: up to 2500 A

Material: PBT

Fire protection: UL 94-V0

Continuous operating temperature: 140 °C

Bar centre distance: 150 mm

Tightening torques

Assembly screw: 8 - 10 Nm

Lid attachment: 5 - 10 Nm