


Rittal – The System.

Faster – better – everywhere.



SK 3172.100

Chopped-fibre filter mat

State: 17/01/2026 (Source: [ittal.com/ie-en](https://www.ittal.com/ie-en))



SK 3172.100 - Chopped-fibre filter mat

Spare filter mats for roof-mounted fans, fan-and-filter units or thermoelectric coolers, for effective protection of enclosure components from dirt, dust and water.

Features

Model No.	SK 3172.100
Design	for filter fans
Product description	Made of chopped-fibre mat with a progressive structure. Temperature-resistant to 100 °C, self-extinguishing category F1 to DIN 53 438. Dust-laden air side: Open structure. Clean-air side: Closed structure. Reliable filtering of virtually all types of dust from a particle size of 10 µm.
Material	Chemical fibres
Note	No suitable for use in EMC filter fans.
To fit Model No.	3240.... 3241....
Dimensions	Width: 221 mm Height: 221 mm Depth: 17 mm
Filter class	to DIN EN 779: G3 to DIN EN ISO 16890: ISO Coarse 50%
Packs of	5 pc(s).
Net weight	0.095
Gross weight	0.1
Customs tariff number	56039390
EAN	4028177038097
E-Number Sweden	E3404745
ETIM 9	EC002513
ETIM 8	EC002513

Features

ECLASS 8.0 27180706

Approvals

Approvals UR + C-UR (recognized)

Certificates EAC