

**Rittal – The System.**

Faster – better – everywhere.



**SK 3240.066**

**Chopped-fibre filter mat**

State: 23/05/2026 (Source: [rittal.com/ie-en](http://rittal.com/ie-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3240.066 - Chopped-fibre filter mat

Spare filter mats for roof-mounted fans, fan-and-filter units or thermoelectric coolers, for effective protection of enclosure components from dirt, dust and water.

## Features

|                       |  |
|-----------------------|--|
| Model No.             | SK 3240.066  |
| Design                | for EMC filter fans  |
| Product description   | Made of chopped-fibre mat with a progressive structure. Temperature-resistant to 100 °C, self-extinguishing category F1 to DIN 53 438. Dust-laden air side: Open structure. Clean-air side: Closed structure. Reliable filtering of virtually all types of dust from a particle size of 10 µm. |
| Material              | Copper-nickel-chrome coated chemical fibres  |
| Note                  | Performance data, protection category and device approvals are only guaranteed when used in conjunction with original Rittal filter mats.  |
| To fit Model No.      | 3240.6..<br>3241.6..   |
| Dimensions            | Width: 226 mm<br>Height: 226 mm<br>Depth: 17 mm  |
| Filter class          | to DIN EN 779: G3  |
| Packs of              | 5 pc(s).   |
| Net weight            | 0.09 kg  |
| Gross weight          | 0.095 kg   |
| Customs tariff number | 56039390   |
| ETIM 9                | EC002513   |
| ETIM 8                | EC002513   |
| ECLASS 8.0            | 27180706   |

# Features

---

|                     |  |
|---------------------|--|
| Product description | SK spare filter mats, for EMC-filter fans, for SK 3240.6../3241.6..,<br>WHD: 226 x 226 x 17 mm |
|---------------------|--|

# Approvals

---

|           |                        |
|-----------|------------------------|
| Approvals | UR + C-UR (recognized) |
|-----------|------------------------|