


Rittal – The System.

Faster – better – everywhere.



SK 3300.180 Aisle containment

State: 13/03/2026 (Source: rittal.com/ie-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3300.180 - Aisle containment

Door and roof components separate hot and cold air in the data centre. Such a separation is pivotal to increasing the efficiency of climate control technology. It may be used as a hot or cold aisle containment.

Features

Model No.	SK 3300.180
Design	Roof element centre
Product description	Slimline door element with viewing window and sliding door. Stable roof elements in a composite material with a high level of light permeability. Where required, safety glass may also be used. The aisle width is 1,200 mm.
Benefits	Increased energy efficiency and performance capability of climate control Easily installed and retrofitted, as it is fully compatible with the VX IT rack system An inexpensive way to boost the performance of your existing installation, lengthening the investment cycle until a replacement needs to be purchased
Applications	Depending on the application, aisle containment may be used with CRAC systems or LCP Inline as hot or cold aisle containment
Function principle	Aisle containment is a combination of door and roof components which facilitate consistent separation of the hot and cold air in the data centre. Such separation is pivotal to saving energy and increasing the efficiency of the available climate control technology.
Material	Sheet steel, spray-finished
Colour	RAL 7035
Dimensions	Width: 800 mm Depth: 1,200 mm
Note	Compartment Rack VX IT (Model No. 531x.175, 531x.185) is not compatible with this product. Contact us for alternative solutions.
Packs of	1 pc(s).

Features

Net weight	11 kg
Gross weight	23 kg
Customs tariff number	73269098
ETIM 9	EC002525
ETIM 8	EC002525
ECLASS 8.0	27182102

Tender text

Roof element for cold aisle containment
Roof element for cold aisle containment with a cold aisle width of 1200 mm and a server rack width of 800 mm consisting of a steel/safety glass compound.
The clear height of cold aisle is 2200 mm.