
Rittal – The System.

Faster – better – everywhere.





SK 3301.390 Vertical shielding

State: 14/12/2025 (Source: rittal.com/ie-en)



SK 3301.390 - Vertical shielding for TS IT

To block the airflow on the left and right of the 482.6 mm (19") level, for enclosure height 2000 mm.

Features

| Model No. | SK 3301.390 |
|-----------------------|---|
| Design | Self-adhesive on one side |
| Product description | To block the airflow on the left and right of the 482.6 mm (19") level, for enclosure height 2000 mm. |
| Material | Cellular PU foam Flame-inhibiting to UL 94 (HF1) |
| Colour | Anthracite |
| Sealing between | Side panel and 482.6 mm (19") level |
| Dimensions | Width: 184 mm Height: 1,910 mm Depth: 84 mm |
| To fit | Width: 800 mm |
| Packs of | 1 pc(s). |
| Net weight | 0.818 |
| Gross weight | 0.918 |
| Customs tariff number | 39269097 |
| EAN | 4028177507999 |
| ETIM 9 | EC002620 |
| ETIM 8 | EC002620 |
| ECLASS 8.0 | 27189261 |
| | |

Tender text

© Rittal 2025

Thin foam rubber, 800 mm rack, vertical LCP shielding

Cellular PU foam, flame-inhibiting to UL 94 (HF1) to block the airflow on the left and right of the 82.6 mm (19 inch) level. For 800 mm wide enclosures.

Length: 1900 mm, self-adhesive

Packs of 1

© Rittal 2025 3