


Rittal – The System.

Faster – better – everywhere.



HD 4000.082

Viewing window HD

State: 14/09/2025 (Source: rittal.com/ie-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



HD 4000.082 - Viewing window HD

For the protection of switches or displays.

Features

| | |
|-------------------------------------|---|
| Model No. | HD 4000.082 |
| Product description | For the protection of switches or displays. |
| Benefits | Large viewing panel Gap-free transition between the viewing window and the frame External hinge With T handle for easy opening without a key |
| Material | Frame: Stainless steel 1.4301 (AISI 304) Seal: Silicone, compliant with FDA Guideline 21 CFR 177.2600 Viewing window: Polycarbonate |
| Supply includes | 2 hinges T handle Assembly parts |
| Visible area | Viewing window width: 352 mm Viewing window height: 185 mm |
| Dimensions | Width: 470 mm Height: 290 mm Depth: 65 mm |
| To fit | Enclosure type: HD compact enclosure |
| IP protection category to IEC 60529 | IP 55 |
| IK Code | IK08 |
| Installation options | For external mounting on surfaces. |
| Type rating to UL 50E | Type 1 Type 12 Type 13 |
| Packs of | 1 pc(s). |
| Net weight | 2.84 |

Features

| | |
|-----------------------|---------------|
| Gross weight | 2.896 |
| Customs tariff number | 39252000 |
| EAN | 4028177985162 |
| ETIM 9 | EC002527 |
| ETIM 8 | EC002527 |
| ECLASS 8.0 | 27182204 |