Rittal – The System.

Faster - better - everywhere.





AS 4050.745 Wire end ferrules

State: 4/11/2025 (Source: rittal.com/ie-en)



AS 4050.745 - Wire end ferrules loose

With plastic collar.

Features

Model No.	AS 4050.745
Product description	With plastic collar.
Technical specifications	Heat-resistant to 105 °C
Material	E-Cu, galvanic tin-plated Plastic collar: Polypropylene
Colour	Black
Length	8 mm
AWG	16
Internal diameter	4 mm
For cross-section	1.5 mm²
DIN colour code	Yes
Multinorm	Yes
Note	UL-certified in conjunction with the relevant tools, such as crimping machines. For bespoke advice, please contact your Rittal sales consultant.
Delivery form	Loose
Packs of	500 pc(s).
Net weight	0.5
Gross weight	0.5
Customs tariff number	85369010
EAN	4028177805132
ETIM 9	EC000005
ETIM 8	EC000005

© Rittal 2025

Features

ECLASS 8.0 36659290

Approvals

Approvals UL + C-UL (listed) UR

© Rittal 2025

3