


Rittal – The System.

Faster – better – everywhere.



AS 4051.537 Wire end ferrules

State: 2/08/2025 (Source: rittal.com/ie-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4051.537 - Wire end ferrules on a reel

With plastic collar.

Features

Model No.	AS 4051.537
Product description	With plastic collar.
Technical specifications	Heat-resistant to 105 °C
Material	E-Cu, galvanic tin-plated Plastic collar: Polypropylene
Colour	White
Length	10 mm
AWG	18
Internal diameter	3.4 mm
Rittal colour code	Yes
For cross-section	0.75 mm ²
Multinorm	Yes
Note	UL-certified in conjunction with the relevant tools, such as crimping machines.
Delivery form	Taped
Packs of	4,000 pc(s).
Net weight	4
Gross weight	0.584
Customs tariff number	85369010
EAN	4028177937857
ETIM 9	EC000005
ETIM 8	EC000005
ECLASS 8.0	36659290

Approvals

Approvals

UL + C-UL (listed)