

Rittal – The System.

Faster – better – everywhere.



AS 4051.625 Wire end ferrules

State: 27/07/2025 (Source: rittal.com/ie-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4051.625 - Wire end ferrules loose

With plastic collar.

Features

Model No.	AS 4051.625
Product description	With plastic collar.
Technical specifications	Heat-resistant to 105 °C
Material	E-Cu, galvanic tin-plated Plastic collar: Polypropylene
Colour	Yellow
Length	18 mm
AWG	10
Internal diameter	6.3 mm
DIN colour code	Yes
Note	UL-certified in conjunction with the relevant tools, such as crimping machines. For bespoke advice, please contact your Rittal sales consultant.
Standards	AEH DIN 46228
Delivery form	Loose
Packs of	100 pc(s).
Net weight	0.1
Customs tariff number	85369010
EAN	4028177000728
ETIM 9	EC000005
ETIM 8	EC000005
ECLASS 8.0	36659290

Approvals

Approvals

UL + C-UL (listed)

UR