


Rittal – The System.

Faster – better – everywhere.



AS 4051.698 Wire end ferrules

State: 15/09/2025 (Source: rittal.com/ie-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4051.698 - Wire end ferrules on a reel

With plastic collar.

Features

Model No.	AS 4051.698
Product description	With plastic collar.
Technical specifications	Heat-resistant to 105 °C
Material	E-Cu, galvanic tin-plated Plastic collar: Polypropylene
Colour	Black
Length	10 mm
AWG	16
Internal diameter	3.5 mm
For cross-section	1.5 mm ²
DIN colour code	Yes
Note	UL-certified in conjunction with the relevant tools, such as crimping machines.
Standards	AEH DIN 46228
Delivery form	Taped
Packs of	5,000 pc(s).
Net weight	5
Customs tariff number	85369010
EAN	4028177938687
ETIM 9	EC000005
ETIM 8	EC000005
ECLASS 8.0	36659290

Approvals

Approvals

UL + C-UL (listed)