Rittal – The System.

Faster - better - everywhere.





AS 4054.001 Crimping pliers

State: 17/11/2025 (Source: rittal.com/ie-en)



AS 4054.001 - Crimping pliers for wire end ferrules

For use with wire end ferrules with no insulating collar to DIN 46228 Part 1 and wire end ferrules with insulating collar to DIN 46228 Part 4.



Features

Model No.	AS 4054.001
Design	Angled
Product description	For use with wire end ferrules with no insulating collar to DIN 46228 Part 1 and wire end ferrules with insulating collar to DIN 46228 Part 4.
Benefits	Minimal effort required with large wire cross-sections Uniformly high quality compression Marked die stations for precise machining of the relevant cross- sections Releasable ratchet
Material	High-quality special tool steel
Surface finish	Matt, plated
Colour	Handle: Anthracite and Rittal Power Pink
Compression	Square crimp
Direction of cable entry	Front
Dimensions	Height: 59 mm Length: 198 mm
AWG	22 - 10
For cross-section	0.5 - 6 mm²

© Rittal 2025

Features

Packs of	1 pc(s).
Net weight	0.452
Gross weight	0.462
Customs tariff number	82032000
EAN	4028177807594
ETIM 9	EC000168
ETIM 8	EC000168
ECLASS 8.0	21043811

© Rittal 2025 3