

# Rittal – The System.

Faster – better – everywhere.



## AS 4054.002 Crimping pliers

State: 27/06/2026 (Source: [rittal.com/ie-en](http://rittal.com/ie-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4054.002 - Crimping pliers for wire end ferrules

Crimping tool for square or hexagonal compression, for processing wire end ferrules with no insulating collar to DIN 46228, Part 1 and wire end ferrules with insulating collar to DIN 46228, Part 4.

## Features

Model No.	AS 4054.002
Design	Straight
Product description	For use with wire end ferrules with no insulating collar to DIN 46228, Part 1 and wire end ferrules with insulating collar to DIN 46228, Part 4.
Benefits	Minimal effort required with large wire cross-sections Uniformly high quality compression Releasable ratchet Self-adjusting
Material	High-quality special tool steel
Surface finish	Matt, plated
Colour	Handle: RAL 7016 and RAL 35745
Compression	Square crimp
Direction of cable entry	Side
Dimensions	Length: 176 mm
AWG	26 - 8
For cross-section	0.14 - 10 mm <sup>2</sup>
Packs of	1 pc(s).
Net weight	0.4 kg
Gross weight	0.449 kg
Customs tariff number	82032000
ETIM 9	EC000168
ETIM 8	EC000168

# Features

---

ECLASS 8.0

21043811

---

Product description

AS crimping tool, square, for cross-section 0.14 – 10 mm<sup>2</sup>