

**Rittal – The System.**

Faster – better – everywhere.



**AS 4055.070**

**Manual hydraulic punch set, M16 -  
M63**

State: 22/05/2026 (Source: [rittal.com/ie-en](http://rittal.com/ie-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4055.070 - Manual hydraulic punch set, M16 - M63

Manual hydraulic punch in a practical set with hole punches for sheet steel. Maximum machinable material thickness 2 or 3 mm.

## Features

|  |  |
|--|--|
| Model No.  | AS 4055.070  |
| Design   | This set includes the standard hole punches M16 to M63   |
| Product description                                | Manual hydraulic punch in a practical set with hole punches for sheet steel. Maximum machinable material thickness 2 or 3 mm.  |
| Benefits   | Extend tool life with a built-in overpressure valve<br>Hole punches, hydraulic punches and accessories for making round, square and rectangular cut-outs in steel steel and stainless steel                        |
| Supply includes                                    | Manual hydraulic punch, straight<br>7 splitter hole punches, triple splitting<br>Hydraulic screw Ø 19 mm<br>Hydraulic screw Ø 9.5 / 19 mm<br>HSS pilot drill Ø 10 mm<br>Spacer sleeve set (3-part)<br>Plastic case |
| Machinable material                                | Sheet steel  |
| Maximum machinable material thickness, sheet steel | 2 mm<br>2 mm<br>2 mm<br>3 mm<br>3 mm<br>3 mm<br>3 mm   |
| Ø punch  | 16.2 mm<br>20.4 mm<br>25.4 mm<br>32.5 mm<br>40.5 mm<br>50.5 mm<br>63.5 mm  |

# Features

---

|                       |  |
|-----------------------|--|
| For threads           | M16<br>M20<br>M25<br>M32<br>M40<br>M50<br>M63              |
| Packs of              | 1 pc(s).   |
| Net weight            | 5.3 kg   |
| Gross weight          | 5.34 kg  |
| Customs tariff number | 82034000   |
| ETIM 9                | EC002121   |
| ETIM 8                | EC002121   |
| ECLASS 8.0            | 21049046   |
| Product description   | Hand hydraulic punch set straight M16,20,25,32,40,50,63 mm |

---