

Rittal – The System.

Faster – better – everywhere.



PS 4612.000 Levelling feet

State: 18/06/2026 (Source: rittal.com/ie-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



PS 4612.000 - Levelling feet for VX, TS, TS IT, SE, PC, IW, Blue e+ chillers

To compensate for height differences with floor irregularities. Mounting thread M12. Optionally with hex socket for adjustment from the inside of the enclosure.

Features

Model No.	PS 4612.000
Design	without hex socket
Benefits	To compensate for height differences with floor irregularities
Material	Sheet steel
Assembly instruction	A base/plinth adaptor is required for mounting on the VX base/plinth
Max. load capacity (static) per component	3,000 N
Dimensions	Thread: M12 x 40
To fit	Enclosure type: VX TS TS IT VX SE PC IW Blue e+ chillers TX CableNet
Levelling range	18 - 43 mm
Packs of	4 pc(s).
Net weight	0.212 kg
Gross weight	0.229 kg
Customs tariff number	83024900
ETIM 9	EC000721
ETIM 8	EC000721

Features

ECLASS 8.0

27182003

Product description

PS Levelling feet, for TS, TS IT, SE, PC, IW, Blue e+ chillers, TX CableNet, adjustment height 18-43 mm, with M12 thread

Tender text

Levelling feet 18-43 mm high
for TS, TS IT, SE, PC, IW, Chiller Blue e+, TX CableNet
adjustment height 18-43 mm,
assembly thread M12