Rittal - The System.

Faster – better – everywhere.



DK 5301.542 Sheet steel door, one-piece, solid

State: 17/10/2025 (Source: rittal.com/ie-en)



DK 5301.542 - Sheet steel door, one-piece, solid for VX IT

To replace existing doors.



Features

Model No.	DK 5301.542
Product description	To replace existing doors.
Material	Sheet steel
Surface finish	Spray-finished
Colour	Door: RAL 7035
	Comfort handle VX: RAL 9005
Supply includes	Door with comfort handle for semi-cylinders with security lock 3524
	4 x 130° hinges, inside
	Assembly parts
Assembly instruction	For a door opening angle of 180° when baying, a 180° baying hinge is required
Note	Door opening angle for stand-alone siting: max. 165°
	Door opening angle when baying: max. 110°
IP protection category to IEC 60 529	IP 55

© Rittal 2025

Features

To fit	Enclosure type: VX IT Width: = 800 mm Height: = 2,200 mm
Packs of	1 pc(s).
Net weight	34.45
Gross weight	35.4
PCF per pack (cradle-to-gate)	134.9 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
EAN	4028177955097
ETIM 9	EC000747
ECLASS 8.0	27182204

© Rittal 2025 3