


Rittal – The System.

Faster – better – everywhere.



VX 5302.030

Slide rail, 2 U, static installation, heavy duty

State: 5/08/2025 (Source: rittal.com/ie-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 5302.030 - Slide rail, 2 U, static installation, heavy duty for VX IT

For mounting between a front and rear pair of mounting angles for 482.6 mm (19") standard mounting angles and 482.6 mm (19") dynamic mounting angles in the VX IT.



Features

Model No.	VX 5302.030
Product description	Side system punchings for mounting accessories and cooling components that expel to the side.
Benefits	Simply locate into the system punchings of the 482.6 mm (19") mounting brackets after adjusting the required 482.6 mm (19") distance between levels
Applications	For attachment between the front and rear 482.6 mm (19") mounting level To support heavy installed equipment
Material	Sheet steel
Surface finish	Zinc-plated
Supply includes	Assembly parts
Load capacity	2000 N, static
Note	Effective contact surface 35 mm per side
Installation options	for 482.6 mm (19") mounting angles, standard: Distance between levels 320/345 mm for 482.6 mm (19") mounting angles, dynamic: Distance between levels 300/325 mm

Features

Packs of	2 pc(s).
Net weight	1.04
Gross weight	1.04
Customs tariff number	73269098
EAN	4028177952591
E-Number Sweden	E7282590
ETIM 9	EC002620
ECLASS 8.0	27189261