


Rittal – The System.

Faster – better – everywhere.



VX 5302.322 Cable route

State: 23/05/2026 (Source: rittal.com/ie-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 5302.322 - Cable route for VX, VX IT

For cable clamping and routing with network and server applications.



Features

Model No.	VX 5302.322
Benefits	Simple assembly with tool-free quick-release fastening Alternatively suitable for screw-fastening Integral multifunctional punching for attaching cable routing components Integral mounting holes for fixing the PDUs in a 7 U pitch pattern via a keyhole recess
Applications	For vertical cable routing and strain relief with network and server applications
Material	Sheet steel
Surface finish	Spray-finished
Colour	RAL 9005
Supply includes	Assembly parts
Installation options	On the VX IT frame between the roof and base frames, all-round In 800 mm wide VX IT racks, alternatively, screw-fastening between the upper and lower depth stays is supported

Features

Assembly instruction	For mounting across the entire enclosure depth on the frame structure with a quick-release fastener. When mounted in 800 mm wide enclosures, additional screw fastening to the depth-stays of the 482.6 mm (19") configuration is supported
Dimensions	Width: 265 mm
To fit	Enclosure type: VX VX IT Height: ≥ 2,000 mm
Packs of	1 pc(s).
Net weight	6.8 kg
Gross weight	7.12 kg
PCF per pack (cradle-to-gate)	27.8 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	83024200
ETIM 9	EC000047
ECLASS 8.0	27400703
Product description	Cable route, for VX, VX IT, for vertical cable routing and strain relief, for network and server applications, integrated multifunction punchings for fastening