

Rittal – The System.

Faster – better – everywhere.



DK 5501.310 Base mount

State: 21/06/2026 (Source: rittal.com/ie-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 5501.310 - Base mount for TS IT

To accommodate gland plate modules.

Features

Model No.	DK 5501.310
Product description	To accommodate gland plate modules.
Benefits	Tool-free mounting or screw-fastening. Easily retrofitted and combined with stabiliser.
Material	Sheet steel
Surface finish	Spray-finished
Colour	RAL 7035
Supply includes	2 mounting rails including assembly parts.
To fit	Enclosure type: TS IT TX CableNet Depth: 800 mm
Packs of	2 pc(s).
Net weight	1.28 kg
Gross weight	1.6 kg
PCF per pack (cradle-to-gate)	5.7 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	73269098
ETIM 9	EC002620
ECLASS 8.0	27189261
Product description	DK Base mount, 2 mounting rails incl. assembly parts, D: 800 mm, for TS IT, TX CableNet, sheet steel, RAL 7035

Tender text

Base mount

For TS IT, TX CableNet

2 mounting rails, incl. assembly parts

Depth: 800 mm

Sheet steel, RAL 7035