

Rittal – The System.

Faster – better – everywhere.



DK 5502.145 Cable duct

State: 2/04/2026 (Source: rittal.com/ie-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 5502.145 - Cable duct for TS IT, TE

Cable duct with removable duct cover hinged on both sides.



Features

Model No.	DK 5502.145
Product description	Cable duct has a removable duct cover hinged on both sides and is alternatively suitable for screw-fastening.
Benefits	Simple assembly with tool-free quick-release fastening High packing density due to U-based cable routing Suitable for back-to-back baying
Material	Sheet steel Plastic to UL 94-V0
Colour	RAL 9005
Supply includes	Cover and assembly parts incl. 4 cable retainers for spare cables
Units	42 U
To fit	Enclosure type: TS IT TE Width: 800 mm Height: 2,200 mm
Suitable for width	800 mm
Packs of	1 pc(s).
Net weight	8.298 kg
Gross weight	8.735 kg

Features

Customs tariff number	73269098
ECLASS 8.0	27400604
Product description	DK Cable duct, WxH: 800x2200 mm, 42 U, For TS IT, RAL 9005

Tender text

Cable duct, vertical

Cable duct with particularly high packing density due to height unit-based cable routing.

Individual cable routing holders channel the cable bundles per height unit.

Removable duct cover hinged on both sides.

Mounting is possible at the side of the 482.6 mm (19") mounting level, at the front and rear in the enclosure.

Within the duct, a cable holder may be attached to accommodate surplus cables.

Simple assembly with tool-free quick-release fastening on the horizontal sections of the 482.6 mm (19") mounting level. Alternatively suitable for screw-fastening.

May be used for Rittal enclosure series TS IT.

The cable duct is suitable for back-to-back baying.

For enclosure height H=2200 mm, supported installation height 42 U.

Material: Cable duct made of sheet steel,

Cable routing components made of plastic UL 94-V0

Colour: RAL 9005

Model No DK: 5502.145

Manufacturer: Rittal