

# Rittal – The System.

Faster – better – everywhere.



## CP 6321.000

# Operating housing for desktop TFT up to 24"

State: 10/05/2026 (Source: [rittal.com/ie-en](http://rittal.com/ie-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# CP 6321.000 - Operating housing for desktop TFT up to 24"

Integral VESA 75/100 locator. Effective, attractive protection for commercially available desktop TFTs up to 24" in the formats 16:9/16:10. High protection category IP 65.

## Features

|                                     |  |
|-------------------------------------|--|
| Model No.                           | CP 6321.000  |
| Design                              | Viewing window with single-pane safety glass   |
| Product description                 | For the installation of commercially available desktop TFTs with a screen diagonal of up to 24" in the formats 16:9/16:10.   |
| Material                            | Enclosure and door: Sheet steel<br>Handle strips: Aluminium<br>Cover caps: Plastic<br>Viewing window: Single-pane safety glass<br>TFT holder: Sheet steel  |
| Surface finish                      | Enclosure and door: Dipcoat primed, powder-coated on the outside, textured paint<br>Handle strip: Natural anodised   |
| Colour                              | Enclosure and door: RAL 7035<br>Handle strip: Natural anodised<br>Cover caps: similar to RAL 7024  |
| Supply includes                     | Enclosure with cut-out and reinforcement for support arm connection Ø 130 mm<br>Viewing window<br>Holder for desktop TFT with VESA 75/100 locator<br>Side handle strips and cover caps<br>Rear door with r/h hinge<br>Cam lock with 3 mm double-bit insert |
| Dimensions                          | Width: 650 mm<br>Height: 450 mm<br>Depth: 155 mm   |
| IP protection category to IEC 60529 | IP 65  |

# Features

|                       |  |
|-----------------------|--|
| Number of locks       | 1  |
| Note                  | The support arm connection and door hinge may be swapped over by rotating the enclosure<br>Optional: Support arm connection Ø 130 mm, preformed off-centre in the reinforcement plate, easily drilled out<br>Lock insert may be exchanged for 27 mm lock inserts, type A, lock cylinder, plastic handles and T handles, type B |
| Basic material        | Aluminium  |
| Lock                  | Lock version: Cam<br>Number of locks: 1<br>Lock insert: 3 mm double-bit  |
| Packs of              | 1 pc(s).   |
| Net weight            | 16.468 kg  |
| Gross weight          | 17.335 kg  |
| Customs tariff number | 94032080   |
| ECLASS 8.0            | 27180505   |
| Product description   | CP Operating housing for desktop TFT up to 24", WHD: 650x450x155 mm, Sheet steel, handle strips made of aluminum   |

# Approvals

|              |   |
|--------------|---|
| Explanations | Declaration of conformity<br>Declaration of conformity UK |
|--------------|---|