Rittal - The System.

Faster – better – everywhere.






CP 6538.010 Command panel housing with door

State: 4/11/2025 (Source: rittal.com/ie-en)




CP 6538.010 - Command panel housing with door Stainless steel

Command panel housing with door made from stainless steel 1.4301 (AISI 304), with handle strips made from plastic approved for use with foodstuffs. May be combined with support arm system CP40, stainless steel.







Features

Model No.	CP 6538.010
Design	With support arm connection CP 40, stainless steel
Material	Enclosure and door: Stainless steel 1.4301 (AISI 304) Handle strips: Plastic approved for use with foodstuffs, dyed blue
Surface finish	Brushed, grain 400
General colour	Stainless steel
Colour	Handle strips: similar to RAL 5002
Supply includes	Enclosure of all-round solid construction
	Cut-out and reinforcement for support arm system CP 40 stainless steel
	Fastener with guide plate
	Door with sealing frame and side handle strips
	Lock: 3 mm double-bit
Dimensions	Width: 400 mm
	Height: 400 mm
	Depth: 150 mm

© Rittal 2025 2

Features

IP 66
NEMA 12
The support arm connection and door hinge may be swapped over by rotating the enclosure 3 mm double-bit lock insert may be exchanged for 41 mm lock inserts, plastic handles and T handles, type C
Stainless steel 1.4301 (AISI 304)
Matching mounting panel 5050.453 with dispatch bag 5050.507
1 pc(s).
8.84
8.85
94032080
4028177220386
EC002504
27180505

Approvals

Approvals	UL
Explanations	Declaration of conformity
	Declaration of conformity UK

© Rittal 2025 3