

# Rittal – The System.

Faster – better – everywhere.



## TP 6742.500

## One-piece consoles TP

State: 21/06/2026 (Source: [rittal.com/ie-en](http://rittal.com/ie-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# TP 6742.500 - One-piece consoles TP

One-piece consoles TP, ready-to-use component with high protection category IP 55 in four different widths. Tool-free assembly of the cover with a lid stay. Compatibility with TS8 system accessories, such as base/plinths and cable entry grommets.

## Features

|                                   |                                                                                                                                                                                                                                                                     |
|-----------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Model No.                         | TP 6742.500                                                                                                                                                                                                                                                         |
| Material                          | Enclosure: Sheet steel 1.5 mm<br>Door and console cover: Sheet steel, 2.0 mm, all-round foamed-in PU seal<br>Mounting plate: Sheet steel, 3.0 mm                                                                                                                    |
| Surface finish                    | Enclosure, cover and door: Dipcoat-primed, powder-coated on the outside, textured paint<br>Mounting plate: Zinc-plated                                                                                                                                              |
| Colour                            | RAL 7035                                                                                                                                                                                                                                                            |
| Supply includes                   | Enclosure, solid back and sides<br>Door or double door at front, with locking rod<br>Mounting plate<br>Cover hinged at rear, 2 stays with automatic locking. Automatic unlocking on the left, manual unlocking on the right<br>Open base for individual cable entry |
| Dimensions                        | Width: 1,200 mm<br>Height: 973 mm                                                                                                                                                                                                                                   |
| Dimensions mounting plate (W x H) | 1,130 mm x 900 mm                                                                                                                                                                                                                                                   |
| Depth (top)                       | 500 mm                                                                                                                                                                                                                                                              |
| Depth (bottom)                    | 400 mm                                                                                                                                                                                                                                                              |
| Number of doors                   | 2                                                                                                                                                                                                                                                                   |
| IK Code                           | IK08                                                                                                                                                                                                                                                                |
| Note on Model No.                 | With the two-door variant, the base opening is divided in two, and two packs of gland plates are required.                                                                                                                                                          |

# Features

---

|                                     |                                                                                    |
|-------------------------------------|------------------------------------------------------------------------------------|
| IP protection category to IEC 60529 | IP 55                                                                              |
| Protection category NEMA            | NEMA 12                                                                            |
| Basic material                      | Sheet steel                                                                        |
| Dimensions                          | Width: 1,200 mm<br>Height: 973 mm<br>Depth (top): 500 mm<br>Depth (bottom): 400 mm |
| Packs of                            | 1 pc(s).                                                                           |
| Net weight                          | 85.5 kg                                                                            |
| Gross weight                        | 90 kg                                                                              |
| Customs tariff number               | 94032080                                                                           |
| ECLASS 8.0                          | 27180504                                                                           |
| Product description                 | TP one-piece console, WHD1: 1200x960x400/D2: 500 mm, sheet steel                   |

# Approvals

---

|              |                           |
|--------------|---------------------------|
| Approvals    | UL + C-UL (listed)        |
| Explanations | Declaration of conformity |