


**Rittal – The System.**

Faster – better – everywhere.



**DK 7063.850**

**Installation kit, depth-variable**

State: 12/06/2026 (Source: [rittal.com/ie-en](http://rittal.com/ie-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7063.850 - Installation kit, depth-variable for 482.6 mm (19") component shelves

Installation kit for component shelves and drawers, depth-variable.

## Features

Model No.	DK 7063.850
Product description	Depending on the distance between the two 482.6 mm (19") mounting levels, the installation kit is screw-fastened in the depth between the L-shaped mounting angles or 482.6 mm (19") mounting frame.
Material	Sheet steel
Surface finish	Zinc-plated
Supply includes	Assembly parts
Distance between levels	550 - 850 mm
Installation dimensions	Installation depth for components: 482.6 mm Installation width for components: 19"
Packs of	2 pc(s).
Net weight	1.852 kg
Gross weight	2.052 kg
Customs tariff number	83024900
ECLASS 8.0	27189261
Product description	DK Installation kit, depth-variable, For 482.6 mm (19") component shelves, distance between levels: 550-850 mm

# Tender text

Server rails, infinitely adjustable,  
for network enclosures with two 482.6 (19 inch)  
levels.

The length of the server rails is fully adjustable  
between 550 to 850 mm. They are mounted between  
two 482.6 mm (19 inch levels).

Material:

Sheet steel

Surface finish: Zinc-plated, passivated

Length: 550 - 850 mm