

Rittal – The System.

Faster – better – everywhere.



DK 7282.135 Drawer

State: 23/05/2026 (Source: rittal.com/ie-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7282.135 - Drawer for one 482.6 mm (19") mounting level

For front attachment to mounting angles, 482.6 mm (19"). With cover and telescopic slides to accommodate assignment lists, operating manuals and small parts.



Features

| | |
|-------------------------------|--|
| Model No. | DK 7282.135 |
| Product description | For front attachment to mounting angles, 482.6 mm (19"). With cover and telescopic slides to accommodate assignment lists, operating manuals and small parts. The small version of the 2 U variant is also suitable for mounting inside a swing frame. |
| Material | Sheet steel |
| Colour | RAL 7035 |
| Supply includes | Fully assembled Security lock 12321 |
| Clearance depth | 244 mm |
| Clearance width | 411 mm |
| Packs of | 1 pc(s). |
| Net weight | 4.54 kg |
| Gross weight | 4.74 kg |
| PCF per pack (cradle-to-gate) | 18.1 kg CO2 eq (Cat B) |
| Note on PCF category | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |

Features

| | |
|-----------------------|---|
| Customs tariff number | 94039910 |
| ETIM 9 | EC002620 |
| ECLASS 8.0 | 27189261 |
| Product description | DK Drawer, 2 U, For a 482.6 mm (19") attachment level, Installation depth: 250 mm |

Tender text

Keyboard drawer, 482.6 mm (19"), 2 U, 250 mm deep

Material: Sheet steel, spray finished in RAL 7035

Installation depth: 250 mm