

Rittal – The System.

Faster – better – everywhere.



DK 7282.135 Drawer

State: 23/05/2026 (Source: rittal.com/ie-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7282.135 - Drawer for one 482.6 mm (19") mounting level

For front attachment to mounting angles, 482.6 mm (19"). With cover and telescopic slides to accommodate assignment lists, operating manuals and small parts.



Features

Model No.	DK 7282.135
Product description	For front attachment to mounting angles, 482.6 mm (19"). With cover and telescopic slides to accommodate assignment lists, operating manuals and small parts. The small version of the 2 U variant is also suitable for mounting inside a swing frame.
Material	Sheet steel
Colour	RAL 7035
Supply includes	Fully assembled Security lock 12321
Clearance depth	244 mm
Clearance width	411 mm
Packs of	1 pc(s).
Net weight	4.54 kg
Gross weight	4.74 kg
PCF per pack (cradle-to-gate)	18.1 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared

Features

Customs tariff number	94039910
ETIM 9	EC002620
ECLASS 8.0	27189261
Product description	DK Drawer, 2 U, For a 482.6 mm (19") attachment level, Installation depth: 250 mm

Tender text

Keyboard drawer, 482.6 mm (19"), 2 U, 250 mm deep

Material: Sheet steel, spray finished in RAL 7035

Installation depth: 250 mm