


Rittal – The System.

Faster – better – everywhere.



DK 7827.201

Mounting angles, 482.6 mm (19")

State: 16/08/2025 (Source: rittal.com/ie-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7827.201 - Mounting angles, 482.6 mm (19") for TS

L-shaped mounting angles, also for accommodating server system installation kits.

Features

Model No.	DK 7827.201
Design	L-shaped mounting angle
Benefits	Integral U markings in the front facilitate systematic assembly within the 482.6 mm (19") attachment level. L-shaped mounting angles accommodate the installation kits of server systems Suitable for 482.6 mm (19") partial installation
Technical specifications	Integral 482.6 mm (19") punchings (EIA standard) Side round and square punchings Clear chromated for conductive connection of the 482.6 mm (19") installed equipment.
Material	Sheet steel, 2 mm
Supply includes	Assembly parts
Units	42 U
Note	Please select slide rails according to the relevant 482.6 mm (19") distance between levels. If combining with L-shaped mounting angles, a mounting adaptor for L-shaped mounting angles must be used.
To fit	Enclosure type: TS Height: 2,000 mm
Packs of	2 pc(s).
Net weight	4.642
Gross weight	4.842
Customs tariff number	73269098
EAN	4028177234949
E-Number Sweden	E3404324

Features

ETIM 9	EC002620
ECLASS 8.0	27189261

Tender text

DK-TS mounting angles, L-shaped, 42 U

Technical specifications: 2 mm steel sheet, with integrated 482.6 mm (19") punchings as well as 25 mm DIN pitch pattern round and square holes. Zinc-plated, passivated for conductive connection to the installed 482.6 mm (19") equipment.

Material: Sheet steel, zinc-plated, passivated