

# Rittal – The System.

Faster – better – everywhere.



## DK 7955.510

## PDU UK, basic version

State: 22/08/2025 (Source: [rittal.com/ie-en](https://www.rittal.com/ie-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7955.510 - PDU UK, basic version

The compact design allows fast assembly in the zero-U space of TS IT network and server enclosures. Input with CEE connector (16 A/32 A) with BS 1363 (UK) outputs. Distribution output from 3.7 kW to 22 kW.

## Features

|                                   |                                                                                                                                                                                                                                                                      |
|-----------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Model No.                         | DK 7955.510                                                                                                                                                                                                                                                          |
| Product description               | Robust, compact basic power distributor for the IT environment. Thanks to the compact PDU, any IT rack is easily equipped with a professional power distribution system. The TS IT rack even supports tool-free assembly. The compact design allows simple assembly. |
| Material                          | Aluminium section, black anodised                                                                                                                                                                                                                                    |
| Dimensions                        | Width: 44 mm<br>Depth: 62 mm<br>Length: 440 mm                                                                                                                                                                                                                       |
| No. of sockets and type           | 6 x C13 / 1 x C19                                                                                                                                                                                                                                                    |
| Sockets                           | 6 x GB (type G, BS 1363)                                                                                                                                                                                                                                             |
| Rated current (max.)              | 13 A                                                                                                                                                                                                                                                                 |
| Infeeds                           | Qty.: 1<br>Phases per infeed: 1~                                                                                                                                                                                                                                     |
| Length of connection cable        | 3 m                                                                                                                                                                                                                                                                  |
| Type of electrical connection     | UK                                                                                                                                                                                                                                                                   |
| Operating temperature range       | 0 °C...45 °C                                                                                                                                                                                                                                                         |
| Ambient humidity (non-condensing) | 10...95 %                                                                                                                                                                                                                                                            |
| Storage temperature range         | -25 °C...70 °C                                                                                                                                                                                                                                                       |
| To fit                            | Enclosure type: TS IT: ≤ 800 mm                                                                                                                                                                                                                                      |
| Packs of                          | 1 pc(s).                                                                                                                                                                                                                                                             |
| Net weight                        | 1.24                                                                                                                                                                                                                                                                 |

# Features

|                       |               |
|-----------------------|---------------|
| Gross weight          | 1.42          |
| Customs tariff number | 85366990      |
| EAN                   | 4028177685024 |
| ECLASS 8.0            | 27142604      |