

# Rittal – The System.

Faster – better – everywhere.



## AX 7993.147

# Compact enclosure AX

State: 1/08/2025 (Source: [rittal.com/ie-en](http://rittal.com/ie-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AX 7993.147 - Compact enclosure AX Volvo Cars Group standard

Modified as a command panel, dimensions 760 x 760 x 300 mm with integral keyboard rack.

## Features

Model No.	AX 7993.147
Product description	Compact enclosure based on AX 1073.000. Robust sheet steel structure comprising a body folded and welded from a single piece, with all-round protection channel at the door opening, rear panel with eyelets for wall mounting brackets. Enclosure base with sheet steel gland plate. Door with foamed PU seal, vertical perforated door strips on both sides, with PE conductor connection, screw-fastened hinges. Mounting plate: With machined keyhole for earthing, with dimensional markings, secured with ring nuts.
Material	Sheet steel Viewing window: Single-pane safety glass, 3.0 mm
Surface finish	Enclosure and door: Dipcoat primed, powder-coated on the outside, textured paint Mounting plate: Zinc-plated
Colour	RAL 7035
Supply includes	The door has a viewing window in the top section made from single-pane safety glass, 3 mm thick, with a visible area of 543 x 345 mm. Behind the viewing window is a VESA recess (allowing the customer to install a TFT monitor as shown in drawing X198472) fitted with the aid of a U-shaped bracket Below the viewing window are 10 holes Ø 22.5 mm Below the drilled holes is a fitted keyboard drawer with integral mousepad The mousepad support is covered with an 8 mm thick plastic sheet measuring 260 x 206 mm (WxH)
Dimensions	Width: 760 mm Height: 760 mm Depth: 300 mm
Packs of	1 pc(s).

# Features

---

Gross weight	41.5
EAN	4028177962552

---