

Rittal – The System.

Faster – better – everywhere.



TS 8610.625 Glazed door

State: 7/09/2025 (Source: [rittal.com/ie-en](https://www.rittal.com/ie-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TS 8610.625 - Glazed door for TS, TS IT, VX SE

Instead of a sheet steel door or rear panel.



Features

Model No.	TS 8610.625
Product description	Instead of a sheet steel door or rear panel.
Material	Frame: Extruded aluminium section Corner pieces: Die-cast zinc Viewing window: Single-pane safety glass, 3 mm
Surface finish	Powder-coated
Colour	Frame: RAL 7035 Corner pieces: RAL 7035 Viewing window (printed mask on the inside): RAL 9005
Supply includes	Viewing door frame with safety glass Locking rod with double-bit insert 180° hinges (4)
Visible area	Viewing window width: 460 mm Viewing window height: 2,040 mm
Viewing window height	2,040 mm

Features

Assembly instruction	Lock components are required when mounting instead of the rear panel
IP protection category to IEC 60529	IP 55
To fit	Enclosure type: TS TS IT VX SE Width: = 600 mm Height: = 2,200 mm
Packs of	1 pc(s).
Net weight	15.7
Gross weight	16.2
EAN	4028177693869
ETIM 9	EC000747
ECLASS 8.0	27182204