


Rittal – The System.

Faster – better – everywhere.



VX 8620.095

Base/plinth trim panels with brush strip

State: 23/05/2026 (Source: rittal.com/ie-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 8620.095 - Base/plinth trim panels with brush strip for base/plinth system VX

The 100 mm high base/plinth trim panels are used in the width or depth for cable entry into the base/plinth. The trim panels may also be used in a 200 mm high base/plinth and combined with other 100 mm high trim panels.

Features

| | |
|-----------------------|---|
| Model No. | VX 8620.095 |
| Product description | For cable entry in the base/plinth. With a base/plinth height of 200 mm, one or two trim panels with brush strips may optionally be used. Thanks to the complete symmetry of the base/plinth system VX, the trim panels with brush strip may either be fitted at the front, rear or side on the base/plinth corner piece. |
| Material | Base/plinth trims: Sheet steel Brush strip: Plastic, self-extinguishing |
| Colour | RAL 9005 |
| Supply includes | Assembly parts |
| Dimensions | Height: 100 mm |
| To fit | Width/depth: 1,200 mm |
| Type rating to UL 50E | Type 1, 12 |
| Weight/pack | 2.8 kg |
| Packs of | 2 pc(s). |
| Net weight | 2.5 kg |
| Gross weight | 2.8 kg |
| Customs tariff number | 94039910 |
| ETIM 9 | EC000721 |
| ECLASS 8.0 | 27182003 |
| Product description | VX Base/plinth trim panel, with brush strip, for W/D: 1200 mm |

Approvals

Approvals

UL + C-UL - FTTA