Rittal - The System.

Faster – better – everywhere.





VX 8660.090 Base/plinth trim panels, vented

State: 15/11/2025 (Source: rittal.com/ie-en)



VX 8660.090 - Base/plinth trim panels, vented for base/plinth system VX, sheet steel

For venting the enclosure via the base/plinth. With a 200 mm base/plinth height, one or two vented trim panels may optionally be used. Thanks to the optional trim panel attachment, the vented trim panels may also be fitted at the side of the base/plinth corner piece.

Features

Model No.	VX 8660.090	
Design	Vented	
Material	Sheet steel	
Colour	RAL 9005	
Supply includes	Assembly parts	
Dimensions	Height: 100 mm	
To fit	Enclosure type: VX VX IT VX SE TX CableNet TS TS IT TP PC IW CX To fit width/depth: 600 mm	
Type rating to UL 50E	Type 1 Type 12	
Weight/pack	1.42 kg	
Packs of	2 pc(s).	
To fit	for base/plinth system VX, sheet steel	
Net weight	1	
Gross weight	1.319	

© Rittal 2025

2

Features

Customs tariff number	94039910
EAN	4028177982949
ETIM 9	EC000721
ETIM 8	EC000721
ECLASS 8.0	27182003

Approvals

Explanations	PCF-declaration	

© Rittal 2025 3