## Rittal – The System.

Faster - better - everywhere.





# SV 9340.260 OM supports

State: 31/10/2025 (Source: rittal.com/ie-en)



## SV 9340.260 - OM supports without contact system

For mounting of switchgear with external power supply.

#### **Features**

Model No.	SV 9340.260
Product description	For mounting of switchgear with external power supply.
Material	Polyamide Fire protection corresponding to UL 94-V0
Colour	Chassis: RAL 7035
For bar systems with centre-to- centre spacing	60 mm
Support rail type	Support frame, PinBlock
Number of poles	3-pole
PinBlock	Yes
Dimensions	Width: 45 mm Height: 208 mm
To fit busbars	Height: 5, 10 mm
Support frame (W x H)	45 mm x 170 mm
Packs of	1 pc(s).
Net weight	0.219
Gross weight	0.22
Customs tariff number	85369095
EAN	4028177504363
ETIM 9	EC001166
ECLASS 8.0	27400607

© Rittal 2025

### **Approvals**

Approvals	ABS
	DNV-GL
	Lloyds Register of Shipping
	UL + C-UL (listed)
Explanations	Declaration of conformity
	Declaration of conformity UK

#### Tender text

OM support (without contact system)

OM support without contact system (3-pole)

for busbar thickness 5/10 mm and PLS 800/1600

Technical specifications

Construction width: 55 mm

Length: 208 mm

Support frame: 45 x 170 mm Support frame support: -

PinBlock: yes

System:

Rittal RiLine60

© Rittal 2025