

Rittal – The System.

Faster – better – everywhere.



SV 9340.260 OM supports

State: 30/06/2026 (Source: rittal.com/ie-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9340.260 - OM supports without contact system

For mounting of switchgear with external power supply.

Features

Model No.	SV 9340.260
Design	without contact system
Product description	For mounting of switchgear with external power supply.
Material	Polyamide Fire protection corresponding to UL 94-V0
Colour	Chassis: RAL 7035
For bar systems with centre-to-centre spacing	60 mm
Support rail type	Support frame, PinBlock
Number of poles	3-pole
PinBlock	Yes
Dimensions	Width: 45 mm Height: 208 mm
To fit busbars	Height: 5, 10 mm
Support frame (W x H)	45 mm x 170 mm
Approvals	UL
Packs of	1 pc(s).
Net weight	0.219 kg
Gross weight	0.22 kg
Customs tariff number	85369095
ETIM 9	EC001166
ECLASS 8.0	27400607
Product description	SV OM Support, WH: 45x208 mm, support frame, PinBlock, without contact system

Approvals

Approvals	ABS DNV Lloyds Register UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK

Tender text

OM support (without contact system)
OM support without contact system (3-pole)
for busbar thickness 5/10 mm and PLS 800/1600
Technical specifications
Construction width: 55 mm
Length: 208 mm
Support frame: 45 x 170 mm
Support frame support: -
PinBlock: yes
System:
Rittal RiLine60