Rittal – The System.

Faster – better – everywhere.





SV 9627.000 Mini-PLS component adaptor

State: 8/12/2025 (Source: rittal.com/ie-en)



SV 9627.000 - Mini-PLS component adaptor

Maximum rated current from 12 A to 100 A.

Features

Model No.	SV 9627.000
Material	Polyamide Fire protection corresponding to UL 94-V0
Colour	RAL 7035
Connection cables (AWG)	AWG 10
Rated operating voltage	690 V, 3~
Rated current max.	40 A
Dimensions	Width: 72 mm Height: 160 mm
Support rails Qty/height	1 / 7.5 mm
To fit manufacturer (model)	Eaton PKZ2
Packs of	1 pc(s).
Net weight	0.3
Gross weight	0.385
Copper weight (kg per piece)	0.046
Customs tariff number	85369095
EAN	4028177140998
ETIM 9	EC001531
ECLASS 8.0	27370304

Approvals

© Rittal 2025

Approvals

Approvals	UR + C-UR (recognized)
Explanations	Declaration of conformity
	Declaration of conformity UK

© Rittal 2025 3