

**Rittal – The System.**

Faster – better – everywhere.



**SV 9629.010**

**Mini-PLS component adaptor**

State: 31/05/2026 (Source: [rittal.com/ie-en](http://rittal.com/ie-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9629.010 - Mini-PLS component adaptor

Maximum rated current from 12 A to 100 A.

## Features

|                              |  |
|------------------------------|--|
| Model No.                    | SV 9629.010  |
| Material                     | Polyamide<br>Fire protection corresponding to UL 94-V0   |
| Colour                       | RAL 7035   |
| Connection cables (AWG)      | AWG 12   |
| Rated operating voltage      | 690 V, 3~  |
| Rated current max.           | 25 A   |
| Dimensions                   | Width: 90 mm<br>Height: 160 mm   |
| Support rails Qty/height     | 1 / 7.5 mm   |
| Packs of                     | 1 pc(s).   |
| Net weight                   | 0.42 kg  |
| Gross weight                 | 0.515 kg   |
| Copper weight (kg per piece) | 0.041  |
| Customs tariff number        | 85369095   |
| ETIM 9                       | EC001531   |
| ECLASS 8.0                   | 27370304   |
| Product description          | SV Mini-PLS component adaptor, 25 A, 690 V, 3-pole, connection cable AWG 12, WH: 90x160 mm, support rail H: 7,5 mm |

## Approvals

# Approvals

---

Explanations

Declaration of conformity

Declaration of conformity UK