

Rittal – The System.

Faster – better – everywhere.



SV 9673.692

Partial mounting plates

State: 24/06/2026 (Source: rittal.com/ie-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9673.692 - Partial mounting plates for compartment side panel modules (internal compartmentalisation)

With or without duct, for direct attachment to the functional space side panel modules.



Features

Model No.	SV 9673.692
Design	with gland made from insulating material
Product description	For direct attachment to the compartment side panel modules for internal compartmentalisation. Universal interior installation with switchgear and controlgear. Creation of additional mounting levels. In combination with compartment dividers and side panel modules, internal compartmentalisation in accordance with Form 2, 3 or 4 is possible.
Material	Sheet steel, 2 mm
Surface finish	Zinc-plated
Supply includes	Angle brackets and assembly parts
For compartment height	200 mm
Dimensions	Width: 702 mm Height: 193 mm
To fit	Width: = 800 mm
Packs of	1 pc(s).
Net weight	3.27 kg
Gross weight	3.47 kg

Features

Customs tariff number	73269098
ETIM 9	EC002525
ECLASS 8.0	27400613
Product description	SV Partial mounting plate, WH: 702x193 mm, with duct, for TS (B: 800 mm)