

Rittal – The System.

Faster – better – everywhere.



SV 9677.951 Current transformer

State: 25/05/2026 (Source: rittal.com/ie-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9677.951 - Current transformer

For inductive measurement of current flow.

Features

Model No.	SV 9677.951
Product description	Compact design without altering the installation depth via mechanical integration into the top-mounting components (185 mm centre-to-centre spacing); this allows space-saving assembly.
Material	Polyamide
For size	2/3
To fit Model No.	9677.260 9677.265 9677.280 9677.360 9677.365 9677.380 9677.930
Rated power input	1.5 VA
Type of electrical connection	Box terminal
Insulation material (class)	H
Primary current	400 A
Secondary current	5 A
Accuracy Class	1
Test specification	IEC 60 044-1 EN 60715 DIN VDE 0414 DIN 42 600-2
Connection of round conductors	2.5 - 4 mm ²
Rated frequency	50 - 60 Hz
Packs of	1 pc(s).

Features

Net weight	0.136 kg
Gross weight	0.146 kg
Customs tariff number	85043129
ETIM 9	EC002048
ECLASS 8.0	27141146
Product description	SV current transformer 400 A/5 A for NH slimline switch-disconnector size 2-3 / adaptor for RiLine Compact (SV 9677.XXX)