

Rittal – The System.

Faster – better – everywhere.



SZ 9765.249 Ground plinth

State: 21/05/2026 (Source: rittal.com/ie-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 9765.249 - Ground plinth for multifunctional enclosures

Stainless steel ground plinth for multifunctional enclosures.

Features

Model No.	SZ 9765.249
Material	Stainless steel 1.4016 (AISI 430)
Surface finish	Enclosure: Powder-coated, UV-resistant pure polyester
Colour	RAL 7035
Supply includes	Assembly parts
Dimensions	Width: 1,300 mm Height: 660 mm Depth: 500 mm
To fit	Enclosure type: MFG 12
Packs of	1 pc(s).
Net weight	43 kg
Gross weight	58 kg
Customs tariff number	94039910
ETIM 9	EC000721
Product description	SZ Ground plinth for multifunctional enclosure MFG 12, for W: 1300 mm, D: 500 mm, stainless steel

Tender text

Ground Plinth for MFC 12

Plinth system for outdoor installation, consisting of Basic housing, and 4x base feet.

Housing and base feet made of 2 mm stainless steel 1.4016.

Completely powder coated in
RAL 7035 pure polyester.
Material: stainless steel 1.4016
Surface: powder coated in RAL 7035, pure polyester
Dimensions: WHT 1300x 600 x 500
Brand: Rittal
Type: ground base for MFC 12 or equivalent
Manufacturer: Rittal GmbH & Co. KG