

Rittal – The System.

Faster – better – everywhere.



KL 1528.010

Terminal boxes KL

State: 8/2/2026 (Source: rittal.com/in-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



KL 1528.010 - Terminal boxes KL Stainless steel

Terminal boxes, stainless steel 1.4301 (AISI 304), Protection category IP 66.

Features

| | |
|-----------------------------------|---|
| Model No. | KL 1528.010 |
| Material | Enclosure: Stainless steel 1.4301 (AISI 304) Cover: Stainless steel 1.4301 (AISI 304), all-round foamed-in PU seal |
| Surface finish | Enclosure and cover: Brushed, grain 180 |
| Supply includes | Enclosure with cover Quick-release fastener including plastic bushes |
| Protection category NEMA | NEMA 4X |
| Protection category to IEC 60 529 | IP 66 |
| IK Code | IK08 |
| Dimensions | Width: 200 mm Height: 200 mm Depth: 120 mm |
| Material thickness - cover | 1.25 mm |
| Material thickness - enclosure | 1.25 mm |
| Lock | Number of locks: 4 |
| Basic material | Stainless steel 1.4301 (AISI 304) |
| Packs of | 1 pc(s). |
| Net weight | 2 |
| Gross weight | 2.151 |
| Customs tariff number | 84879090 |
| EAN | 4028177663336 |
| E-Number Sweden | E3404379 |
| ETIM 9 | EC000261 |
| ETIM 8 | EC000261 |

Features

ECLASS 8.0

27180101

Approvals

| | |
|-----------|--|
| Approvals | Bureau Veritas DNV-GL UL + C-UL (listed) |
|-----------|--|

| | |
|--------------|---|
| Explanations | Declaration of conformity Declaration of conformity UK |
|--------------|---|