

Rittal – The System.

Faster – better – everywhere.



KL 1531.510

Terminal boxes KL

State: 25/1/2026 (Source: [ittal.com/in-en](https://www.ittal.com/in-en))



FRIEDHELM LOH GROUP

KL 1531.510 - Terminal boxes KL with gland plate

Spray-finished enclosure with sheet steel cover, with gland plate. Protection category IP 55.



Features

Model No.	KL 1531.510
Material	Enclosure: Sheet steel Cover: Sheet steel, all-round foamed-in PU seal
Surface finish	Enclosure and cover: Dipcoat primed, powder-coated on the outside, textured paint
Colour	RAL 7035
Supply includes	Enclosure with cover Quick-release fastener including plastic bushes Sheet steel gland plates with seals and assembly parts
Protection category NEMA	NEMA 12
Protection category to IEC 60 529	IP 55
IK Code	IK08
Dimensions	Width: 300 mm Height: 200 mm Depth: 120 mm
Material thickness - cover	1.25 mm
Material thickness - enclosure	1.25 mm
Gland plates	: 1 + 1 Size of gland plate for bus enclosures, position top/bottom: 2
Basic material	Sheet steel

Features

Packs of 1 pc(s).

Net weight 3

Gross weight 3.119

Customs tariff number 73269098

EAN 4028177251373

E-Number Sweden E3404687

ECLASS 8.0 27180101

Approvals

Approvals Bureau Veritas
DNV-GL
Lloyds Register of Shipping
UL + C-UL (listed)

Explanations Declaration of conformity UK