


Rittal – The System.

Faster – better – everywhere.



EB 1557.500

E-Box EB

State: 7/7/2025 (Source: rittal.com/in-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



EB 1557.500 - E-Box EB

Wall-mounted enclosure with door and mounting plate of sheet steel. Protection category IP 66. With 180° hinge. Lock insert may also be exchanged for individual lock systems.

Features

Model No.	EB 1557.500
Material	Enclosure and door: Sheet steel, all-round foamed-in PU seal
Surface finish	Enclosure and door: Dipcoat primed, powder-coated on the outside, textured paint Mounting plate: Zinc-plated
Colour	RAL 7035
Supply includes	Enclosure with hinged door 180° hinge Cam lock with 3 mm double-bit insert Mounting plate
Protection category NEMA	NEMA 4
Protection category to IEC 60 529	IP 66
IK Code	IK08
Dimensions	Width: 200 mm Height: 500 mm Depth: 120 mm
Dimensions mounting plate (W x H)	175 mm x 485 mm
Material thickness - enclosure	1.25 mm
Material thickness - door	1.25 mm
Material thickness of mounting plate	2 mm
Lock	Lock version: Cam Number of locks: 2 Lock insert: 3 mm double-bit
Basic material	Sheet steel

Features

Packs of	1 pc(s).
Net weight	5.292
Gross weight	5.571
Customs tariff number	94032080
EAN	4028177251762
E-Number Sweden	E3404652
ECLASS 8.0	27180101

Approvals

Approvals	Bureau Veritas C-UL Lloyds Register of Shipping UL UL + C-UL (listed)
Explanations	Manufacturer's declaration Declaration of conformity Declaration of conformity UK

Tender text

E Box, protection category IP 66

Enclosure:

Sturdy sheet steel construction, of 1.38 mm sheet steel, folded and welded from a single piece, with all-round protection channel on the door aperture, with recessed holes for wall mounting brackets in the rear panel.

Doors:

1.5 mm - 2 mm sheet steel, sealed, with foamed-in seal and screw-fastened hinges, 180° opening angle, cam lock with double-bit insert to DIN 43668.

Mounting plate:

2 or 2.5 mm sheet steel, zinc-plated

Accessories:

Lock systems, wall mounting brackets, earth straps

Surface finish:

Steel is cleaned, degreased, phosphated, electrophoretic dipcoat-primed and polyester powder-coated in textured RAL 7035, pale grey.

Dimensions (W x H x D): 200 x 500 x 120 mm