Rittal – The System.

Faster – better – everywhere.





HD 1684.630 Switch housing HD

State: 15/11/2025 (Source: rittal.com/in-en)




HD 1684.630 - Switch housing HD

Enclosure solution with cut-outs for switches, tailored to the requirements of the food and beverage industry. All-round gap-free silicone seal between enclosure and cover. Hygienecompliant quick-release hexagon fastener.







Features

HD 1684.630
Hygienic Design enclosure
Hygienic Design enclosure
Enclosure and cover: Stainless steel 1.4301 (AISI 304) 1.5 mm
Screw plug: Stainless steel
Seal: Silicone, compliant with FDA Guideline 21 CFR 177.2600
Enclosure and cover: Brushed, grain 400, peak-to-valley height
< 0.8 μm
Seal: Blue, dyed (RAL 5010)
Enclosure of all-round solid construction
Cover with switch cut-out
Seal and screw plug (supplied loose)
Width front: 100 mm
Width (rear): 122 mm
Height, front: 280 mm
Height rear: 302 mm
Depth: 90 mm
60 mm
4 x 30.5 mm

© Rittal 2025

Features

IK Code	IK08
Basic material	Stainless steel 1.4301 (AISI 304)
Lock	Lock version: Hygiene-compliant quick-release hexagon fastener Number of locks: 4
IP protection category to IEC 60	IP 66 IP X9
529	IP A9
Protection category NEMA	NEMA 1
	NEMA 3
	NEMA 3X
	NEMA 4
	NEMA 4X
	NEMA 12
	NEMA 13
Type rating to UL 50E	Type 1
	Type 3
	Type 3X
	Type 4
	Type 4X
	Type 12
	Type 13
Packs of	1 pc(s).
Net weight	1.9
Gross weight	1.99
Customs tariff number	84879090
EAN	4028177995451
ETIM 9	EC002713
ETIM 8	EC002713
ECLASS 8.0	27180101

© Rittal 2025 3