


# Rittal – The System.

Faster – better – everywhere.



undefined 2260.965

## AX wall-mounted enclosure, 3-part

State: 4/7/2025 (Source: [rittal.com/in-en](https://www.rittal.com/in-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# undefined 2260.965 - AX wall-mounted enclosure, 3-part With Blue e+ outlet filter

The delivery concept behind the three-part AX wall-mounted enclosures reduces complexity and enhances flexibility. The AX/VX modular system makes these enclosures suitable for a range of applications. The three-part structure ensures easy access.



## Features

|                 |  |
|-----------------|--|
| Model No.       | 2260.965   |
| Design          | Wall-mounted enclosures IT   |
| Material        | Wall and hinged part: Sheet steel, 1.5 mm<br>Viewing window: Single-pane safety glass, 3 mm  |
| Surface finish  | Powder-coated  |
| Colour          | Wall and hinged part: RAL 7035<br>Glazed door: RAL 7035/7015 (slate grey)  |
| Supply includes | Wall section: Gland plate, solid, top and bottom<br>Hinged part with 25 mm pitch pattern of holes in the front and rear frame, and two 482.6 mm (19") mounting angles, front, static installation<br>Designer glazed door<br>Designer glazed door lock: Security lock 3524 E<br>Centre part lock: 3 mm double-bit<br>Including earthing and assembly parts<br>2 Blue e+ outlet filters (supplied loose)<br>Mini-comfort handle |

# Features

|  |   |
|--|---|
| Units                                  | 9 U   |
| Dimensions                             | Width: 600 mm<br>Height: 478 mm<br>Depth: 673 mm                                  |
| Number of locks                        | 1   |
| IK Code                                | IK08  |
| Load capacity of hinged part (static)  | 450 N   |
| Load capacity of wall section (static) | 150 N   |
| Basic material                         | Sheet steel   |
| Lock                                   | Lock version: Mini-comfort handle<br>Lock insert: Security lock insert no. 3524 E |
| Protection category to IEC 60 529      | IP 54 in conjunction with solid gland plate top and bottom                        |
| Customs tariff number                  | 94032080  |
| EAN                                    | 4028177994089   |