

Rittal – The System.

Faster – better – everywhere.



SG 2368.010 Connection component

State: 5/4/2026 (Source: rittal.com/in-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SG 2368.010 - Connection component for signal pillar, modular

Optionally for conduit or wall/base mounting, with cover for optical components.

Features

Model No.	SG 2368.010
Design	for wall/base mounting
Product description	Optionally for conduit or wall/base mounting. Screw terminals in the connection component. With cover for optical components. Contact hazard protection to VDE.
Benefits	Simple assembly and contact via bayonet fastener.
Function principle	A modular layout is possible with connection, optical and acoustic components, incandescent lamps and a label panel
Material	Enclosure of polyamide
Colour	Black
Diameter	70 mm
Rated impulse withstand voltage, phase to phase	2500 V AC
Rated insulation voltage	250 V AC
Signal pillar	modular
Dimensions	Height: 43 mm
Protection category to IEC 60 529	IP 54
Rated operating voltage	12 V - 240 V (AC/DC)
Packs of	1 pc(s).
Net weight	0.11 kg
Gross weight	0.123 kg
Customs tariff number	85369095
ECLASS 8.0	27371232

Features

Product description

SG Connection element, for signal pillar, modular, for wall/base mounting

Approvals

Approvals

UL + C-UL (listed)
UR