

# Rittal – The System.

Faster – better – everywhere.



## SZ 2370.550

## LED flashing light component

State: 22/11/2025 (Source: [rittal.com/in-en](http://rittal.com/in-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SZ 2370.550 - LED flashing light component for signal pillar, modular

With 360° signal transmission thanks to optimised prism system, number of potential stages = 5 components, with identical voltage.

## Features

|                                                 |                                                                                                                                                                                                                                                                    |
|-------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Model No.                                       | SZ 2370.550                                                                                                                                                                                                                                                        |
| Design                                          | LED flashing light component                                                                                                                                                                                                                                       |
| Product description                             | With 360° signal transmission thanks to optimised prism system.<br>Number of potential stages = 5 components, with identical voltage.                                                                                                                              |
| Benefits                                        | Simple assembly and contact via bayonet fastener.<br>Configuration of up to five components with the same voltage.<br>Components are available in a range of colours and voltages.<br>Flashing and stroboscopic light element incl. lamp, suitable for direct use. |
| Function principle                              | A modular layout is possible with connection, optical and acoustic components, incandescent lamps and a label panel                                                                                                                                                |
| Material                                        | Enclosure of polyamide<br>Cap: Transparent polycarbonate                                                                                                                                                                                                           |
| Colour                                          | Red                                                                                                                                                                                                                                                                |
| Diameter                                        | 70 mm                                                                                                                                                                                                                                                              |
| Rated impulse withstand voltage, phase to phase | 2500 V AC                                                                                                                                                                                                                                                          |
| Rated insulation voltage                        | 250 V AC                                                                                                                                                                                                                                                           |
| Dimensions                                      | Height: 56 mm                                                                                                                                                                                                                                                      |
| Protection category to IEC 60 529               | IP 54 if a cover or acoustic component is fitted at the top                                                                                                                                                                                                        |
| Rated operating voltage                         | 230 V                                                                                                                                                                                                                                                              |
| Packs of                                        | 1 pc(s).                                                                                                                                                                                                                                                           |
| Net weight                                      | 0.08                                                                                                                                                                                                                                                               |

# Features

|                       |               |
|-----------------------|---------------|
| Gross weight          | 0.083         |
| Customs tariff number | 94054990      |
| EAN                   | 4028177656505 |
| ECLASS 8.0            | 27371220      |

# Approvals

|           |                          |
|-----------|--------------------------|
| Approvals | UL + C-UL (listed)<br>UR |
|-----------|--------------------------|