


Rittal – The System.

Faster – better – everywhere.



SG 2372.100

Signal pillar LED compact

State: 25/7/2025 (Source: rittal.com/in-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SG 2372.100 - Signal pillar LED compact

Extremely long service life of the LEDs, minimal assembly work and low warehousing costs.

Features

Model No.	SG 2372.100
Design	3-stage, red, yellow, green
Product description	Transmission angle: 3 x 120°, supplied state: Steady light. Flashing function controllable via PLC
Benefits	Complete, ready-to-connect solution Minimal build height Long LED service life Minimal assembly work and warehousing costs
Cable entry	Min. cable diameter: 3 mm Max. cable diameter: 6.5 mm
Diameter	72 mm
Type of electrical connection	Screw terminals
Light	LEDs
Rated insulation voltage	< 60 V DC
Dimensions	Height: 177 mm
Operating temperature range	-20 °C...70 °C
Protection category to IEC 60 529	IP 65
Rated operating voltage	24 V 24 V (DC)
Packs of	1 pc(s).
Net weight	0.339
Gross weight	0.34
Customs tariff number	85318070
EAN	4028177442719

Features

ECLASS 8.0	27371230
------------	----------

Approvals

Approvals	UR
Explanations	Declaration of conformity Declaration of conformity UK