

Rittal – The System.

Faster – better – everywhere.



SZ 2500.100 LED system light

State: 29/4/2024 (Source: rittal.com/in-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 2500.100 - LED system light

LED system light – the first light especially for enclosures! Highly innovative LED technology for even more light into the very last corner.

Features

| | |
|---------------------------|--|
| Model No. | SZ 2500.100 |
| Design | Without socket |
| Benefits | Optimum illumination of the entire enclosure Optionally with clip, screw and magnetic attachment A configuration to suit every application |
| Design | Without socket |
| Material | Light body: Extruded aluminium Light cover: Polycarbonate Light ends: PC-ABS |
| Colour | Enclosure: RAL 7016 |
| Supply includes | Assembly screws |
| Power consumption | 5 W |
| Connection options | Infeed, 2-pole Through-wiring, 2-pole Door-operated switch |
| Protection class | II (all-insulated) |
| Light – installation type | Screw-fastening Clip attachment Magnetic attachment (accessory) |
| Installation options | The internal mounting rail AX and the mounting bracket are required when installing in compact enclosures |
| Luminous flux | 400 lm |
| Light colour | 4000 K (neutral white) |
| Note | Connection accessories should be ordered separately |

Features

| | |
|-------------------------------------|--|
| Dimensions | Width: 262 mm Height: 55 mm Depth: 23 mm |
| Operating temperature range | -20 °C...55 °C |
| Rated operating voltage | 100 V - 240 V, 1~, 50 Hz/60 Hz |
| IP protection category to IEC 60529 | IP 20 |
| Packs of | 1 pc(s). |
| Weight/pack | 0.289 kg |
| Customs tariff number | 94054990 |
| EAN | 4028177806931 |
| E-Number Sweden | E3465308 |
| ETIM 7.0 | EC000321 |
| ECLASS 8.0 | 27189241 |

Approvals

| | |
|--------------|---|
| Approvals | ENEC |
| Explanations | Declaration of conformity Declaration of conformity UK |