## Rittal – The System.

Faster – better – everywhere.





5 (Source: rittal.com/in-en)



## SZ 2561.010 - Plastic cable gland plates with metric knockouts

With pre-punched holes for cable glands.

## **Features**

Model No.	SZ 2561.010
Product description	With pre-punched holes for cable glands. Use seal for standard gland plates.
Colour	RAL 7035
Note	The allocation of gland plate sizes is indicated on the relevant enclosures
No. of metric knockouts	3 x M16 5 x M20 4 x M25 2 x M32 2 x M40
Dimensions	Width: 330 mm Depth: 90 mm
To fit	Enclosure type: AE
Gland plate	Size: 3
Operating temperature range	-40 °C70 °C
Protection category to IEC 60 529	IP 55 if installed correctly
Number knockouts	3 5 4 2 2

© Rittal 2025

## **Features**

Metric diameter	M16
	M20
	M25
	M32
	M40
Packs of	10 pc(s).
Net weight	1.13
Gross weight	1.396
Customs tariff number	39269097
EAN	4028177550261
E-Number Sweden	E3404762
ETIM 9	EC000211
ETIM 8	EC000211
ECLASS 8.0	27142421

© Rittal 2025 3