## Rittal – The System.

Faster – better – everywhere.





## AX 2584.100 Pole clamp

State: 5/11/2025 (Source: rittal.com/in-en)



# AX 2584.100 - Pole clamp for AX, KX, AX plastic, AX IT, CS wall-mounted enclosures

For reliable, convenient fastening to round or square poles.





#### **Features**

Model No.	AX 2584.100
Product description	For reliable, convenient fastening to round or square poles
Technical specifications	For pole diameter: Ø from 40 to 170 mm
	For pole size:   from 50 to 150 mm
Material	Mounting angles, clamping section: Sheet steel
	Clamping strap: Stainless steel 1.4301 (AISI 304)
Surface finish	null
Supply includes	2 mounting angles, 600 mm long
	4 clamping sections
	2 clamping straps
	4 clamping brackets
	4 self-tapping M10 bolts for mounting onto the enclosure
Note	Only suitable for enclosures up to a width of 600 mm.

© Rittal 2025

### Features

To fit	Enclosure type: AX
	KX
	AX plastic
	AX IT
	CS wall-mounted enclosures
	AX outdoor housing
	AE
	KL
	EB
	AX wall-mounted enclosure, 3-part
Type rating to UL 50E	Type 1
	Type 3R
	Type 4
	Type 12
Packs of	2 pc(s).
Net weight	1.88
Gross weight	1.96
PCF per pack (cradle-to-gate)	7.3 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	83024900
EAN	4028177940598
E-Number Sweden	E3465274
ETIM 9	EC002620
ETIM 8	EC002620
ECLASS 8.0	27189234

## Approvals

Approvals	UL + C-UL - FTTA
- Ipp	

© Rittal 2025 3