

Rittal – The System.

Faster – better – everywhere.



TP 2685.600

One-piece consoles

State: 2/9/2025 (Source: rittal.com/in-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TP 2685.600 - One-piece consoles Stainless steel

Stainless steel one-piece consoles 1.4301, (AISI 304), ready-to-use unit with high protection category IP 55 in four different widths. Easy handling thanks to self-latching lid stay. Interchangeable lock insert. Easy cable entry thanks to divided gland plates



Features

| | |
|-----------------------------------|---|
| Model No. | TP 2685.600 |
| Material | Enclosure: Stainless steel 1.4301 (AISI 304), 1.5 mm Door or double door and console lid: Stainless steel 1.4301 (AISI 304), 2.0 mm Mounting plate: Sheet steel, 3.0 mm |
| Surface finish | Enclosure, door, console lid and gland plates: Brushed, grain 400 Mounting plate: Zinc-plated |
| Supply includes | Enclosure, solid back and sides Door or double door at front, with locking rod Console lid with lid stay and cam lock latched in the enclosure Locks with double-bit insert Gland plates, divided Mounting plate |
| Dimensions | Width: 1,000 mm Height: 960 mm |
| Dimensions mounting plate (W x H) | 930 mm x 780 mm |
| Depth (top) | 480 mm |

Features

| | |
|-------------------------------------|--|
| Depth (bottom) | 400 mm |
| Number of doors | 2 |
| IP protection category to IEC 60529 | IP 55 |
| Protection category NEMA | NEMA 12 |
| Basic material | Stainless steel 1.4301 (AISI 304) |
| Dimensions | Width: 1,000 mm Height: 960 mm Depth (top): 480 mm Depth (bottom): 400 mm |
| Packs of | 1 pc(s). |
| Net weight | 77.115 |
| Gross weight | 79.5 |
| Customs tariff number | 94032080 |
| EAN | 4028177031395 |
| ETIM 9 | EC000784 |
| ETIM 8 | EC000784 |
| ECLASS 8.0 | 27180504 |

Approvals

| | |
|--------------|---|
| Approvals | TÜV UL + C-UL (listed) |
| Explanations | Declaration of conformity Declaration of conformity UK |